

Quick Start

M₃e

Installation

- Connect the gas inlet to a gas bottle equipped with a regulator. The gas inlet is an Oxygen Adaptor (9/16-18 R.H).
- Connect the data wiring (Male XLR-5 connector for DMX/RDM) if you are using a DMX or RDM controller.
- Connect the power cord 100-250 VAC, 50/60 Hz, 715W.
- Open the gas bottle (CO₂ or N₂ industrial grade, over 99% of purity), and set the regulator pressure between 50 and 60 psi (3.5 and 4.1 bar, or 350 and 410 kPa).
- Fill the reservoir with MDG Neutral Fog Fluid.

Power on the MDG M3e.

Working with the keyboard (LOCAL Mode)

- Verify the communication mode in the «INTERFACE
 COMM. ». When the «AUTO» mode is activated, the
 MDG *M3e* is then controlled by DMX, only if there is a signal. If the DMX wire is unplugged, the control remains local.
- When the generator is manually switched to **«UNIT ON»** mode («CONTROL ► UNIT ► ON»), the program starts the heating cycle for approximately 8 minutes («STATUS ► STATE = % HEAT»).

When the temperature reaches operating level, the Automatic Purging System[™] (APS[™]) will be initiated («STATUS ► STATE = PURGE»).

After the first purging cycle is completed (1 min), the generator is ready to produce fog («STATUS ▶ STATE = READY»).

To produce Fog, switch the generator to «FOG ON» mode («CONTROL ➤ FOG ➤ ON»).

The MDG **M3e** will start to produce fog right away.

Fog emission can be controlled by adjusting the working pressure of the internal reservoir («CONTROL ▶ PRESSURE»).

The MDG **M3e** will produce fog as long as the control parameters are within specifications, the fog fluid reservoir filled and the gas bottles pressurized.


If a critical problem occurs, the fog generator <u>automatically shuts down</u>, and displays an error message in the **Status Menu**. The most common errors are (check the manual for more details):

ERROR = P. LOW
 Gas bottle is probably closed, empty or not connected. Check also the regulator pressure.

• ERROR = P. HIGH The input gas pressure is too high (Pressure between 50-60 psi / 3.5-4.1 bar / 350-410 kPa).

• ERROR = HEATER Check the AC voltage.

• ERROR = PCB HIGH Move the generator to a colder location.



Working with DMX/RDM Control (DMX Mode)

- Connect a DMX line to DMX In connector (Male XLR-5 connector).
- Select the communication mode in the «INTERFACE → COMM. ». When the «AUTO» mode is activated, the MDG *M3e* is then controlled by DMX, only if there is a DMX signal.
- Set the DMX Start Address in the Interface Menu («INTERFACE ▶ COMM. ▶ DMX ADDR»), and choose any value between 1 and 510 (512, last DMX channel).

The DMX Start Address can be reassigned via a RDM control.

The generator uses two (2) or three (3) DMX channels, depending on its personality:

Personality M3e


•	Channel 1	0 (0%)	< UNIT OFF	≤ 128 (50%)	< UNIT ON	≤ 255 (100%)
•	Channel 2	0 (0%) – 255	(100%), FOG O	UTPUT (from minim	um to maximum)	
•	Channel 3	0 (0%)	< FOG OFF	< 128 (50%)	< FOG ON	< 255 (100%)

Personality MAX 3000

 Channel 1 	0 (0%)	< UNIT OFF	≤ 128 (50%)	< UNIT ON	≤ 255 (100%)
 Channel 2 	0 (0%)	< FOG OFF	≤ 128 (50%)	< FOG ON	< 255 (100%)

Technical Specifications

Total Running Time:	1.3 hours at 2.76 bar / 40 psi			
-	2.5 hours at 1.38 bar / 20 psi			
Fluid consumption:	1.9 l (53.1 oz / 0.475 US gal) per hour at 2.76 bar / 40 psi			
	1.0 l (29.5 oz / 0.264 US gal) per hour at 1.38 bar / 20 psi			
Fluid type:	MDG Neutral[™] Fog Fluid ONLY			
	M.S.D.S. available on request			
Fluid reservoir:	2.5 l (0.66 US gal) bottle			
Gas type:	Industrial Grade CO ₂ or N ₂			
Gas pressure input:	4.15 bar / 60 psi max			
Gas consumption:	1.6 kg (3.53 lb) per hour at 2.76 bar / 40 psi			
	0.96 kg (2.12 lb) per hour at 1.38 bar / 20 psi			
Operating voltage:	100-250 VAC, 50/60Hz, 1 phase, 715 W			
	Ground / Earth connection REQUIRED			
Operating temperature:	0 °C to 50 °C (32 °F to 122 °F)			
Operating humidity:	90 % relative humidity @ 50 °C (122 °F), non-condensing			
Storage temperature:	-40 °C (-40 °F) to 60 °C (140 °F)			
Storage humidity:	80% relative humidity @ 60° C (140 °F)			
Approval	CE, CSA and UL pending			
Dimensions	30 cm (12") H x 18 cm (7") W x 61 cm (24") L			
Weight:	15.6 kg (35 lb)			



... For further details, please read the User Guide.